

For - BEVERAGE & FOOD / COSMETIC / PHARMACEUTICALS / CHEMISTRY / METROLOGY

BT ETA TORQUE ECO - Dynamometric Torque Bottle

DESIGNED TO control torque on Torquetesters

Our Torquemeters are designed with a special mechanical system for measuring torque which cancels most non- coaxial and top load influences on the measurement. These features cancel most operator influences on the measurement for maximum repeatability.





The new AT2E BT ETA TORQUE ECO has been developed in order to allow operators and calibration team to check in a fast way the accuracy of any torquetesters.

Easy to use, just install the BT ETA TORQUE BOTTLE on the Torquetester's measurement table and turn slowly and smoothly in opening or closing direction.

Then just compare the value on your equipment to the BT ETA TORQUE ECO torques setting

Technical specifications:

- Adjustable torque from 1 to 15 Kgf.cm / Inch.lbs
- · Measurements in opening and closing directions
- Delivered with calibration certificate (Option)
- · No battery needed
- Transport case

Mechanical specifications:

- · Aluminum made (Stainless steel on request)
- Dimensions: Customize
- · Weight: 1- 4 kg

MIZE